


DuPont™ Cyrel® 1000 ECLF

State-of-the-Art Exposure, Light Finisher and Post Exposure Unit



[View Hi Res Image](#)

DuPont™ Cyrel® 1000 ECLF



[View Hi Res Image](#)

Floor Plan



Play Video



Download latest version

[DuPont Packaging Graphics](#) continues to be a global technology leader in the development and supply of flexographic printing systems. Our R&D team continues to develop innovative new solutions to help our customers expand their business by taking advantage of new and profitable opportunities in the growing flexographic packaging market. The DuPont Packaging Graphics portfolio of products includes DuPont™ Cyrel® brand photopolymer plates ([analog](#) and [digital](#)), Cyrel® platemaking equipment, [Cyrel® round sleeves](#), [Cyrel® plate mounting systems](#) and the revolutionary [Cyrel® FAST thermal system](#).

DuPont™ Cyrel® Systems: Higher quality at high speed.

The DuPont™ Cyrel® 1000 ECLF is designed with customer needs in mind; it is easy to install, support, maintain and operate. It is robust, extremely cost effective and reliable.

DuPont™ Cyrel® 1000 ECLF

Benefits

- Maximum plate size 36" x 48" (900 x 1,200 mm)
- Light integrator controlled exposure
- Clamshell design
- Outstanding vacuum draw down
- Anodized temperature controlled exposure bed
- Optimum productivity

Product Features

DuPont™ Cyrel® 1000 ECLF can expose, post-expose and finish high quality photopolymer plates up to a format of 36" x 48" (900 x 1,200 mm).

The Exposure section is a clamshell design holding 24 UV-A fluorescent tubes with built-in reflectors. One yellow control tube illuminates the exposure bed for inspection of the plate surface. Unique to this exposure unit is the anodized temperature controlled bed, closed loop system that controls the exposure bed temperature, which translates into predictable and consistent expo-

sure. The unit is fitted with a light integrator that compensates for the decrease in light output as the tubes age. To meet the demanding needs of high quality plates, the user can easily customize the 25 basic exposure set-ups.

Each tube is constantly monitored by a light guide, giving the operator a visual indication. There are three counters imbedded in the PLC to keep track of the number of hours the UV-A and UV-C tubes have been in operation.

The Post Exposure and Light Finisher section hold 19 UV-C and 20 UV-A tubes. The PLC allows the user to perform post exposure and finishing simultaneously. The post exposure and finisher section has 25 basic set-ups that can be easily customized by the user.

DuPont™ Cyrel® 1000 ECLF

State-of-the-Art Exposure, Light Finisher and Post Exposure Unit

Technical Data		
General	Details	Other Notes
Equipment Name	DuPont™ Cyrel® 1000 ECLF	Cooled exposure, post exposure and light finisher
SAP Article Number	MH74451A	
Plate Thickness	0.019" to 0.27"	0.5 mm to 7.0 mm
Max. Nominal Plate Width	36" (900 mm)	
Max. Nominal Plate Length	48" (1,200 mm)	
UV-A Tubes Wave Length	360 nm – 380 nm	
UV-C Tubes Wave Length	254 nm	
Electrical (Field Configurable)	370 / 440 Volt – 50 / 60 hz 208 / 240 Volt – 50 / 60 hz	3Ph / N / PE 3Ph / PE
Power (nominal)	10 kW	
Current (Nominal Load)	16 Amp @ 400 Volt; 26 Amp @ 230 Volt	
Connecting Wires	400 Volt configuration; 230 Volt configuration	5 x 4 mm ² ; 4 x 4 mm ²
Grounding	≤ 0.1 Ω	
Exhaust (Light Finisher)	Ø 5.5" (140 mm)	800 m ³ / h (min)
Environmental Data	Temperature range: 63°F to 82°F (17°C to 28°C)	Relative humidity from 10% to 80% non-condensing
Compressed Air Supply	NA	
Dimensions	Uncrated	Crated
L	61.0" (1,550 mm)	65.0" (1,650 mm)
W	70.9" (1,800 mm)	74.8" (1,900 mm)
H	41.8" (1,060 mm)	59.0" (1,500 mm)
H - open	72.9" (1,850 mm)	
Weight	1,764 lbs (700 kg)	2,138 lbs (970 kg)
Color	DuPont Grey & DuPont Red	

For more information on DuPont™ Cyrel® or other DuPont Packaging Graphics products, please contact your local representative:

www.cyrel.com/na

United States

DuPont Packaging Graphics
Chestnut Run Plaza, Bldg. 702
974 Centre Road
Wilmington, DE 19805
800-345-9999

Canada

DuPont Packaging Graphics
1919 Minnesota Court
Mississauga, ON L5N 0C9
Canada
905-816-3238