

DuPont™ Pyralux® LF Coverlay

flexible composites

Technical Information

Description

DuPont™ Pyralux® coverlay composites are constructed of DuPont Kapton® polyimide film, coated on one side with a proprietary B-staged modified acrylic adhesive. Coverlay is used to encapsulate etched details in flexible and rigid-flex multilayer constructions for environmental and electrical insulation.

Construction

Coverlay is available in a variety of film and adhesive thicknesses. **Table 1** lists typical constructions. The product code must be used when ordering coverlay from DuPont.

Table 1
Coverlay Product Codes

Product Code	Adhesive	Kapton®	IPC
	Mil (µm)	Mil (µm)	Certification*
LF0110	1 (25)	1 (25)	Yes
LF0120	1 (25)	2 (51)	Yes
LF0130	1 (25)	3 (76)	Yes
LF0150	1 (25)	5 (127)	Yes
LF0210	2 (51)	1 (25)	Yes
LF0220	2 (51)	2 (51)	Yes
LF0230	2 (51)	3 (76)	Yes
LF0250	2 (51)	5 (127)	Yes
LF0310	3 (76)	1 (25)	Yes
LF7001	1/2 (13)	1/2 (13)	Yes
LF7013	1 (25)	1/2 (13)	Yes
LF7082	2 (51)	1/2 (13)	No
LF1510	1/2 (13)	1 (25)	Yes
LF7034	1-1/2 (38)	1 (25)	Yes

*Certified to IPC-4203/1: "Adhesive Coated Dielectric Films for Use as Cover Sheets for Flexible Printed Circuitry and Flexible Adhesive Bonding Films."

Packaging

Pyralux® coverlay composites are supplied on 24-inch (610 mm) wide by 250 feet (76 m) long rolls, on nominal 3-inch (76 mm) cores. Narrower widths or cut sheets are available by special order.

Typical Data

Each manufactured lot, except the four coverlay constructions noted in **Table 1**, is certified to IPC specifications and tested according to IPC Test Method TM-650. See **Table 2**.

Table 2
Coverlay Properties vs IPC Specifications

IPC Property	Coverlay Spec	Typical Value
Peel Strength, min., lb/in (kg/cm) As received After solder	8 (1.4) 7 (1.3)	10 (1.8) 10 (1.8)
Dimensional Stability, max., percent	0.10	+0.07
Adhesive Flow, max. mil/mil adhesive (µm/µm)	5.0 (127)	4.2 (107)
Dielectric Constant, max. (at 1 MHz)	4.0	3.6
Dissipation Factor, max. (at 1 MHz)	0.03	0.02
Volume Resistivity, min., megohm-cm (ambient)	10 ⁷	10 ⁹
Surface Resistivity, min., megohm-cm (ambient)	10 ⁶	10 ⁸

*Laminating Conditions: 14kg/cm² (200 psi), 182°C (360°F), 1 hour to treated side of 1 oz RA copper foil. The values in Table 2 represent a typical 1 oz copper foil, 1 mil adhesive and 1 mil Kapton® construction.

A Certificate of Analysis is available with every batch. Complete material and manufacturing records for each lot, with samples of finished laminate, are retained for reference purpose. The roll labels contain the lot number, DuPont order number, customer order number, IPC specification, customer specification, and customer part number; save these labels for reference in case of inquiries.

Processing

Laminating conditions for Pyralux® flexible composites are typically in the following ranges:

Part Temperature:	182–199°C (360–390°F)
Pressure:	14–28 kg/cm ² (200–400 psi)
Time:	1–2 hours, at temperature

For further processing information contact your DuPont representative to receive a Pyralux® Technical Manual.



The miracles of science™

Storage Conditions and Warranty

DuPont™ Pyralux® LF flexible laminates should be stored in the original packaging at temperatures of 4–29°C (40–85°F) and below 70% humidity. The product should not be frozen and should be kept dry, clean and well protected. Subject to compliance with the foregoing handling and storage recommendations, the DuPont warranty, as provided in the DuPont Standard Conditions of Sale, shall remain in effect for a period of two years following the date of shipment.

Safe Handling

Pyralux® coverlay composites contain a B-staged adhesive. Because B-staged adhesive contains trace quantities (parts per million) of unreacted monomers, precautions and recommendations should be taken to minimize contact.

DuPont is not aware of anyone developing contact dermatitis, or suffering any other medical discomforts, when using Pyralux® products. The uncured acrylic monomers in the bond ply adhesive may impart a mild odor. However, these products have been extensively tested under operating conditions (drilling and lamination conditions) and found to liberate measurable volatiles only well below¹ accepted safe limits (e.g., PEL).

For more information on DuPont™ Pyralux® flexible circuit materials, please contact your local representative, or visit our website:

Americas

DuPont Electronic Technologies
14 T. W. Alexander Drive
Research Triangle Park, NC 27709
Tel: 800-243-2143

Europe, Middle East & Africa

DuPont de Nemours (Luxembourg) s.à r.l.
Rue Général Patton, Contern
L-2984 Luxembourg
Tel: +352 3666 5935

Japan

DuPont KK
Sanno Park Tower
11-1, Nagata-cho 2-chome
Chiyoda-ku, Tokyo 100-6111
Tel: 81-3-5521-8660

Taiwan

DuPont Taiwan Hsinchu Branch.
#2, Li-Hsin 4th Rd., Hsinchu Science Park,
Hsinchu 30078, Taiwan
Tel: 886-3-5793654

India

E.I.DuPont India Limited
1001-1012 “Meadows”, 10th Floor
Sahar Plaza Complex
Andheri-Kurla Road, Andheri (East)
Mumbai 400 059, India
Tel: 91-22-6751-5000
DID: 91-22-6751-5038
Fax : 91-22-67101937

China

DuPont China Holding Co., Ltd.
Shanghai Branch
Bldg. 11, 399 Keyuan Road
Zhangjiang Hi-Tech Park
Pudong New District
Shanghai 201203, China
Tel: 86-21-38622720

To eliminate contact between the skin and exposed adhesive after etching, wear lint-free gloves or fingerpads. Anyone handling Pyralux® should wash their hands with soap before eating, smoking, or using restroom facilities. Gloves and fingerpads should be changed daily, and wash other protective clothing frequently.

Adequate ventilation and exhaust is recommended in press rooms to prevent the buildup of potentially harmful vapors, to remove disagreeable odors, and to dissipate heat. Drill rooms should be furnished with standard equipment recommended by drill vendors and required by OSHA standards.

For further information on safe handling, refer to DuPont publication H-46873, “Pyralux® LF and FR Safe Handling;” and refer to “Industrial Ventilation,” 18th Edition or latest available from the American Conference of Governmental Industrial Hygienists, 6500 Glenway, Building D-5, Cincinnati, OH 45211.

¹Values for all materials monitored were well below 10% of their accepted limits (PEL or TLV). In only one case, did the concentration reach approximately 40% of its limit. This was an oven used to dry the uncured acrylic material. This oven drying is not normally used in the process and during the exposure the oven was unventilated. Adequate ventilation is normally recommended for any heating process.

Korea

DuPont Korea Inc.
4/5 Floor, Asia Tower
#726, Yeoksam-dong, Kangnam-ku,
Seoul
135-082 Korea
Tel: 82-2-2222-5224

Singapore

DuPont Singapore Pte, Ltd.
1 HarbourFront Place #11-01
HarbourFront Tower One
Singapore 098633
Tel: 65-6586-3091

pyralux.dupont.com

Copyright ©2012 DuPont or its affiliates. All rights reserved. The DuPont Oval, DuPont™, The miracles of science™, Pyralux® and Kapton® are registered trademarks or trademarks of E.I. du Pont de Nemours and Company or its affiliates.

NO PART OF THIS MATERIAL MAY BE REPRODUCED, STORED IN A RETRIEVAL SYSTEM OR TRANSMITTED IN ANY FORM OR BY ANY MEANS ELECTRONIC, MECHANICAL, PHOTOCOPYING, RECORDING OR OTHERWISE WITHOUT THE PRIOR WRITTEN PERMISSION OF DUPONT.

Caution: Do not use in medical applications involving permanent implantation in the human body. For other medical applications, see “DuPont Medical Caution Statement,” H-50102.

This information is based on data believed to be reliable, but DuPont makes no warranties, express or implied, as to its accuracy and assumes no liability arising out of its use. The data listed herein falls within the normal range of product properties but should not be used to establish specification limits or used alone as the basis of design. Because DuPont cannot anticipate or control the many different conditions under which this information and/or product may be used, it does not guarantee the usefulness of the information or the suitability of its products in any given application. Users should conduct their own tests to determine the appropriateness of the product for their particular purposes.

This information may be subject to revision as new knowledge and experience become available. This publication is not to be taken as a license to operate under, or recommendation to infringe, any patent.

H-73245-5 06/12



The miracles of science™