Specification Properties of DuPont™ Tyvek® 1073B and 1059B Transition Protocol Materials—English



Property	Comparable Test Method	Units	Current Tyvek® 1073B	Transition Protocol Target Value Tyvek® 1073B	1073B Transition Protocol Typical Value	Current Tyvek [®] 1059B	Transition Protocol Target Value Tyvek° 1059B	1059B Transition Protocol Typical Value
Basis Weight	ASTM D3776 ¹ EN ISO 536 ¹	oz/yd²	2.20 [2.10–2.30]	2.20 [2.10–2.30]	2.20 [2.10–2.30]	1.90 [1.82–1.98]	1.90 [1.82–1.98]	1.90 [1.82–1.98]
Delamination	ASTM D2724 ²	lb _f /in.	0.5 [0.4–0.7]	0.5 [0.3-*]	0.6 [0.4–0.8]	0.5 [0.3–0.7]	0.5 [0.3-*]	0.6 [0.4–0.8]
Gurley Hill Porosity	TAPPI T460 ¹ ISO 5636-5 ³	sec/100 cc	22 [8–36]	~22 [8–36]	22 [8–36]	20 [8–36]	~20 [8–36]	22 [8–36]

NOTES: 1073B and 1059B Transition Protocol typical values represent data from 200 and 100 rolls, respectively, across different line and polymer combinations from a limited number of manufacturing campaigns. Values will be refreshed, as necessary, upon data collection from additional campaigns and long-term variability discernment. Specification properties are controlled to a nominal value and released within specifications. The customer is responsible for determining that Tyvek* is suitable for the intended application. The ranges represent the controlled minimum and maximum values in which the product is released. Specification properties are typical values based on roll averages, with samples taken uniformly across the sheet. These properties are representative for uncoated Tyvek* as sold by DuPont. Any downstream operations, such as coatings applied by sterile packaging manufacturers (SPMs), may change these values.

- 1. Modified sample size.
- 2. Modified for speed and gauge length.
- 3. Modified for sealing fluid characteristics.

^{*}Based on customer feedback, upper limit was not specified.

Miscellaneous Properties of DuPont™ Tyvek® 1073B and 1059B Transition Protocol Materials—English



Property	Comparable Test Method	Units	Current Typical Value Tyvek® 1073B	Transition Protocol Target Value Tyvek® 1073B	1073B Transition Protocol Typical Value	Current Typical Value Tyvek® 1059B	Transition Protocol Target Value Tyvek° 1059B	1059B Transition Protocol Typical Value
Microbial Barrier	ASTM F1608 ASTM F2638	LRV % pMax	>5 <0.3	>5 <0.3	>5 <0.3	>4 <0.5	>4 <0.5	>4 <0.5
Bendtsen Air Permeability	ISO 5636-3	mL/min	572	572	513	671	671	557
Moisture Vapor Transmission Rate	TAPPI T523 ¹	g/m²/24 hr	1615	>1600	>1600	1640	>1600	>1600
Hydrostatic Head	AATCC TM 127 EN 20811 ²	in. H ₂ O	58	58	63	57	57	62
Tensile Strength, MD	ASTM D5035 ³ EN ISO 1924-2 ³	lb _f /in.	44	44	50	38	38	43
Tensile Strength, CD	ASTM D5035 ³ EN ISO 1924-2 ³	lb _f /in.	45	45	49	38	38	42
Elongation, MD	ASTM D5035 ³ EN ISO 1924-2 ³	%	20	20	20	19	19	19
Elongation, CD	ASTM D5035 ³ EN ISO 1924-2 ³	%	24	24	24	23	23	23
Elmendorf Tear, MD	ASTM D1424 EN 21974	lb _f	0.7	0.7	0.7	0.6	0.6	0.7
Elmendorf Tear, CD	ASTM D1424 EN 21974	lb _f	0.8	0.8	0.9	0.7	0.7	0.8
Mullen Burst	ASTM D774 ISO 2758	psi	176	176	179	153	153	150
Spencer Puncture	ASTM D3420 ⁴	inlb _f /in. ²	50	50	59	39	39	44
Opacity	TAPPI T425 ISO 2471 ⁵	%	91	91	92	89	89	92
Thickness (Individual)*	ASTM D1777 ⁶ EN 20534 ⁷ EN ISO 534	mils	7.0	7.0	7.8	6.2	6.2	7.0

NOTES: 1073B and 1059B Transition Protocol typical values represent data across different line and polymer combinations from a limited number of manufacturing campaigns. Values will be refreshed, as necessary, upon data collection from additional campaigns and long-term variability discernment. Miscellaneous properties represent typical values based on roll averages, except for thickness (individual), with samples taken uniformly across the sheet. Thickness (individual) typical values are based on a population of pooled individual data points from multiple rolls. Miscellaneous properties are not controlled in the process, and therefore, are subject to slight changes from "normal" process drift. Customers must conduct their own tests to ensure suitability for the intended application. These properties are representative for uncoated Tyvek* as sold by DuPont. Any downstream operations, such as coatings applied by sterile packaging manufacturers (SPMs), may change these values.

MD = machine direction; CD = cross direction; LRV = log reduction value

- 1. Test conditions: 23°C, 85% RH.
- 2. Rate of use: 60 cm H₂O/min.
- 3. Modified for speed and gauge length.
- 4. Modified for %16-in. (14.28-mm) probe.
- 5. Modified for different backing standards, area and illumination.
- 6. 7.15 psi, 0.625-in. diameter presser foot.
- 7. Surface 2 cm², pressure 14.5 psi (100 kPa).

This information is based upon technical data that DuPont believes to be reliable. It is subject to revision as additional knowledge and experience are gained. DuPont makes no guarantee of results and assumes no obligation or liability in connection with this information. It is intended for use by persons having technical skill for evaluation under their specific end-use conditions at their own discretion and risk. Since conditions of use are outside our control, WE MAKE NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING WITHOUT LIMITATIONS, NO WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE AND ASSUME NO LIABILITY IN CONNECTION WITH ANY USE OF THIS INFORMATION.

This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of DuPont or others covering any material or its use.

Copyright © 2014 DuPont. All rights reserved. The DuPont Oval Logo, DuPont", and Tyvek" are trademarks or registered trademarks of E.I. du Pont de Nemours and Company or its affiliates. (06/14)

^{*}Thickness variability target is equal to, or less than, incumbent products.