

## DuPont™ Nucrel® 30907

### Nucrel® resins Product Data Sheet

#### Description

**Product Description** Nucrel® 30907 is an ethylene acid copolymer resin. The resin is available for use in conventional extrusion coating, coextrusion coating, and extrusion laminating equipment designed to process polyethylene resin. This resin may also be used in conventional blown and cast film extrusion and coextrusion equipment.

#### Restrictions

**Material Status** Commercial: Active

#### Typical Characteristics

**Composition** 9.5% By Weight Acrylic Acid comonomer content

#### Typical Properties

Physical	Nominal Values	Test Method(s)	
*Density ( )	0.94 g/cm <sup>3</sup>	ASTM D792	ISO 1183
*Melt Flow Rate ( 190°C/2.16kg )	7 g/10 min	ASTM D1238	ISO 1133
Thermal	Nominal Values	Test Method(s)	
*Melting Point ( DSC )	98 °C ( 208.4 °F )	ASTM D3418	ISO 3146
Freezing Point ( DSC )	83 °C ( 181.4 °F )	ASTM D3418	ISO 3146
Vicat Softening Point ( )	77 °C ( 170.6 °F )	ASTM D1525	ISO 306

#### Processing Information

\*Maximum Processing Temperature 310 °C ( 590 °F )

**General Processing Information** Nucrel® 30907 is normally processed at melt temperatures ranging from 160° to 185°C (320° to 365°F) in blown film equipment and 235° to 305°C (455° to 580°F) in extrusion coating equipment. Typical extruder profiles are shown below. Actual processing temperatures will usually be determined by either the specific equipment or one of the other polymers in a coextrusion. Nucrel® 30907 can also be used in cast extrusions and coextrusions.

Materials of construction used in the processing of this resin should be corrosion resistant. Stainless steels of the types 316, 15-5PH, and 17-4PH are excellent, as is quality chrome or nickel plating, and in particular duplex chrome plating. Type 410 stainless steel is satisfactory, but needs to be tempered at a minimum temperature of 600°C (1112°F) to avoid hydrogen-assisted stress corrosion cracking. Alloy steels such as 4140 are borderline in performance. Carbon steels are not satisfactory. While stainless steels can provide adequate corrosion protection, in some cases severe purging difficulties have been encountered. Nickel plating has been satisfactory, but experiments have shown that chrome surfaces have the least adhesion to acid based polymers. In recent years, the quality of chrome plating has been deteriorating due to environmental pressures, and the corrosion protection has not always been adequate. Chrome over top of stainless steel seems to provide the best combination for corrosion protection and ease of purging.

If surface properties of the extruded resin require modification (such as, lower C.o.F. for packaging machine processing), refer to the Conpol™ Processing Additive Resins product information guide.

After processing Nucrel®, purge the material out using a polyethylene resin, preferably with a lower melt flow rate than the Nucrel® resin in use.

The "Disco Purge Method" is suggested as the preferred purging method, as this method usually results in a more effective purging process. Information on the Disco Purge Method can be obtained via your DuPont Sales Representative.

Never shut down the extrusion system with Nucrel® in the extruder and die. Properly purge out the Nucrel® with a polyethylene, and shut down the line with polyethylene or polypropylene in the system.

### **Blown Film Processing**

Processing Information

Feed Zone	135 °C ( 275 °F )
Second Zone	160 °C ( 320 °F )
Third Zone	185 °C ( 365 °F )
Fourth Zone	185 °C ( 365 °F )
Fifth Zone	185 °C ( 365 °F )
Adapter Zone	185 °C ( 365 °F )
Die Zone	185 °C ( 365 °F )

### **Nominal Values**

A suggested extruder set temperature profile.

### **Extrusion Coating/Lamination Processing**

Processing Information

Feed Zone	185 °C ( 365 °F )
Second Zone	235 °C ( 455 °F )
Third Zone	260 °C ( 500 °F )
Fourth Zone	285 °C ( 545 °F )
Fifth Zone	285 °C ( 545 °F )
Adapter Zone	285 °C ( 545 °F )
Die Zone	285 °C ( 545 °F )

### **Nominal Values**

A suggested extruder set temperature profile.

FDA Status Information

NUCREL® 30907 complies with Food and Drug Administration Regulation 21 CFR 177.1310(a)(1) - - Ethylene-acrylic acid copolymers, subject to the limitations and requirements therein. This Regulation describes polymers that may be used in contact with food, subject to the finished food-contact article meeting the extractive limitations under the intended conditions of use, as shown in paragraph (b) of the Regulation.

The information and certifications provided herein are based on data we believe to be reliable, to the best of our knowledge. The information and certifications apply only to the specific material designated herein as sold by DuPont and do not apply to use in any process or in combination with any other material. They are provided at the request of and without charge to our customers. Accordingly, DuPont cannot guarantee or warrant such certifications or information and assumes no liability for their use.

Regulatory Information

For information on regulatory compliance outside of the U.S., consult your local DuPont representative.

Safety & Handling

For information on appropriate Handling & Storage of this polymeric resin, please refer to the material Safety Data Sheet..

A Product Safety Bulletin, material Safety Data Sheet, and/or more detailed information on extrusion processing and/or compounding of this polymeric resin for specific applications are available from your DuPont Performance Materials representative.

### **Regional Centres**

DuPont operates in more than 70 countries.

For help finding a local representative, please contact one of the following regional customer contact centers:

#### **Americas**

DuPont Company

#### **Asia Pacific**

DuPont China Holding Co., Ltd.

#### **Europe / Middle East / Africa**

DuPont de Nemours Int'l. S.A.

Chestnut Run Plaza – Bldg. 730  
974 Centre Road  
Wilmington, Delaware  
19805 U.S.A.  
Toll-Free (USA): 1-800-628-6208  
Telephone: 1-302-774-1000  
Fax: 1-302-355-4013

DuPont do Brasil, S.A.  
Alameda Itapecuru, 506  
06454-080 Barueri, SP Brasil  
Telephone: +55 11 4166 8000  
Fax: +55 11 4166 8736

Shanghai Branch  
399 Keyuan Road, Bldg. 11  
Zhangjiang Hi-Tech Park  
Pudong New District, Shanghai  
P.R. China (Postcode: 201203)  
Telephone +86 21 3862 2888  
Fax +86-21-3862-2889

2,Chemin du Pavillon Box 50  
CH-1218 Le Grand Saconnex  
Geneva, Switzerland  
Telephone +41 22 717 51 11  
Fax +41 22 717 55 00

<http://www.dupont.com>

*The data listed here fall within the normal range of properties, but they should not be used to establish specification limits nor used alone as the basis of design. The DuPont Company assumes no obligations or liability for any advice furnished or for any results obtained with respect to this information. All such advice is given and accepted at the buyer's risk. The disclosure of information herein is not a licence to operate under, or a recommendation to infringe, any patent of DuPont or others. Since DuPont cannot anticipate all variations in actual end-use conditions, DuPont makes no warranties and assumes no liability in connection with any use of this information.*

*CAUTION: Do not use DuPont materials in medical applications involving implantations in the human body or contact with internal body fluids or tissues unless the material has been provided from DuPont under a written contract that is consistent with DuPont policy regarding medical applications and expressly acknowledges the contemplated use. For further information, please contact your applications and expressly acknowledges the contemplated use. For our DuPont representative You may also request a copy of DuPont POLICY Regarding Medical Applications H-50103-3 and DuPont CAUTION Regarding Medical Applications H-50102-3.*

*Copyright © 2009 DuPont. The DuPont Oval Logo, DuPont™, The miracles of science™, and trademarks designated with "®" are registered trademarks or trademarks of E.I. du Pont de Nemours and Company or its affiliates. All rights reserved*

Version: 12.0  
Last modified at 8/9/2017 8:19 AM