



AMBERLITE™ FPA40 CI

Food Grade Strong Base Anion Exchanger

Introduction

AMBERLITE FPA40 CI can be used as an alternative to AMBERLITE FPA98 CI or AMBERLITE FPA90 CI to decolorize sugar solutions < 200 ICUMSA.

Whilst a gellular resin, the high moisture content exhibits some of the characteristics of a macro-reticular resin which make AMBERLITE FPA40 CI ideally suited to the reversible uptake of organic color bodies commonly found in sucrose syrups.

AMBERLITE FPA40 CI is a very unique product in that it is a gellular resin (high capacity) with macroreticular characteristics (physical stability). It is an excellent resin of choice for Decolorization of organic color bodies in many bioprocessing applications, including natural product extraction and recovery / decolorization of antibiotics from fermentation broth.

It is extensively used in aminoglycoside purification processes in combination with AMBERLITE FPC3500, and/or AMBERLITE CG50 type 1.

Thanks to AMBERITE FPA40 CI, higher level of purity of aminoglycoside antibiotics can be achieved in a deco-lorization step either pre- or post- purification.

Properties

AMBERLITE FPA40 CI is a type 1 strong base anion exchange resin supplied in the Chloride form. Due to the relatively high moisture content, AMBERLITE FPA40 CI exhibits some of the characteristics of macroreticular resin with good resistance to fouling and osmotic stress. The structure is particularly well suited to reversibly removing relatively large organic molecules from a variety of process streams.

Matrix	Crosslinked polystyrene
Functional groups	Quaternary ammonium
Physical form	Clear yellow beads
Ionic form as shipped	Chloride
Total exchange capacity	≥ 1.0 eq/L (Cl ⁻ form)
Moisture holding capacity	57 to 68 % (Cl ⁻ form)
Shipping weight	700 g/L
Harmonic mean size	0.50 to 0.75 mm
Fines content	< 0.425 mm : 2.0 % max

Suggested Operating Conditions

Operating temperature limit	60°C (OH ⁻ form) / 90°C (Cl ⁻ form)
Minimum bed depth	700 mm
Service flow rate	2 to 8 BV*/h
Regenerants	NaCl** (4-10 %)
Regenerant level	50 to 150 g/L _R
Regenerant flow rate	2 to 8 BV/h
Minimum contact time	30 minutes
Slow rinse	2 BV at regeneration flow rate
Fastrinse	4 to 8 BV at service flow rate

Food processing


As governmental regulations vary from country to country, it is recommended that potential users contact Dow Water & Process Solutions in order to determine the best resin choice, optimum operating and regeneration conditions.

Hydraulic Characteristics

Figure 1 shows the bed expansion of AMBERLITE FPA40 CI, as a function of backwash flow rate and water temperature.

Conversion Factors:

- 1 m/h equals 0.41 USgpm/ft²



For more information about DOW™ resins, call the Dow Water & Process Solutions business:

North America: 1-800-447-4369
Latin America: (+55) 11-5188-9222
Europe: +800-3-694-6367
Italy: +800-783-825
South Africa: +0800 99 5078
Pacific: +8007776 7776
China: +400 889-0789
<http://www.dowwaterandprocess.com>

Notice: No freedom from infringement of any patent owned by Dow or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other governmental enactments. The product shown in this literature may not be available for sale and/or available in all geographies where Dow is represented. The claims made may not have been approved for use in all countries. Dow assumes no obligation or liability for the information in this document. References to "Dow" or the "Company" mean the Dow legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.

