

Fossil Power Plant

Condensate Polisher Product Recommendations

Condensate polishers protect critical boiler components from potential condenser leaks, thereby improving plant reliability. Our ion exchange resins have been the backbone of condensate polishing systems throughout the world for decades. Depending on the chemistry used in the boiler feed water, the right resin combination will help provide the optimum performance in terms of treated condensate purity and cycle run length.

PRODUCT	AMINE	CATION PRE-BED	FEATURES AND RECOMMENDED USES	TYPE	MATRIX	TOTAL VOLUME CAPACITY (eq/L min)	IONIC FORM AS SHIPPED
AmberLite™ HPR4700 OH	NH ₄ / Organic Amine	N/A	This pairing offers the best balance of properties for fossil power plants: high capacity gel type resins, uniform particle size, and high physical stability. Combined with the exceptional separation in mixed beds, this is the go-to pairing for fossil power plants.	SBA	GEL	1.10	OH ⁻
AmberLite™ HPR1300 H		Yes		SAC	GEL	2.00	H ⁺
AmberLite™ HPR550 OH	NH ₄ / Organic Amine	N/A	Most typically used in nuclear power plants, but suitable for fossil plants when the premium grade resins with tight metal specifications are required or preferred. Together, these resins offer exceptional separation in mixed beds, which combined with excellent water quality and resin purity, has made them known throughout the industry as a premium mixed bed pairing in condensate polishing. AmberLite™ HPR650 H Resin is also an excellent choice for cation pre-bed required to handle NH ₄ /amine load.	SBA	GEL	1.10	OH ⁻
AmberLite™ HPR650 H		Yes		SAC	GEL	2.00	H ⁺
AmberLite™ HPR550 OH or AmberLite™ HPR4700 OH	NH ₄ / Organic Amine	N/A	Pairing that offers you one of the highest NH ₄ /amine capacity with good anion protection, allowing enhanced pH for better FAC control. AmberLite™ HPR1600 H Resin provides high NH ₄ /amine capacity for cation pre-bed.	SBA	GEL	1.10	OH ⁻
AmberLite™ HPR1600 H		Yes		SAC	GEL	2.40	H ⁺
AmberLite™ HPR900 OH	NH ₄ / Organic Amine	N/A	Pairing that offers you high NH ₄ /amine capacity with good resistance to anion resin fouling. AmberLite™ HPR1600 H Resin provides high NH ₄ /amine capacity for cation pre-bed. The use of a macroporous anion resin provides excellent resistance to surface fouling and kinetic impairment.	SBA	MACRO	0.80	OH ⁻
AmberLite™ HPR1600 H		Yes		SAC	GEL	2.40	H ⁺
AmberLite™ HPR900 OH	NH ₄ / Organic Amine	N/A	Pairing that offers you high capacity with good resistance to anion resin fouling. The use of a macroporous anion resin provides excellent resistance to surface fouling and kinetic impairment.	SAC	MACRO	1.70	OH ⁻
AmberLite™ HPR1300 H		Yes		SAC	GEL	2.00	H ⁺
AmberLite™ HPR9000 OH	Organic Amines	N/A	Pairing that offers you high Na selectivity for operation past amine break. The use of a macroporous anion resin provides excellent resistance to surface fouling and kinetic impairment.	SBA	MACRO	0.80	OH ⁻
AmberLite™ HPR2000 H		No		SAC	MACRO	1.70	H ⁺
AmberLite™ HPR900 OH	NH ₄ / Organic Amine	N/A	Macro resin pairing that combines excellent physical stability with superior resistance to fouling for enhanced resin life. Recommended for use in oxidative conditions or with alternative amines or when high stability needed. This pair is designed for use when a balance of operating performance, simple operation, long resin life, and cost-effective operation is required.	SBA	MACRO	0.80	OH ⁻
AmberLite™ HPR252 H		Yes		SAC	MACRO	1.65	H ⁺
AmberLite™ HPR900 OH	NH ₄ / Organic Amine	N/A	Macro resin pairing designed to be used when a combination of exceptional physical stability, simple and reliable operation, and long resin life is required. Recommended for use in oxidative conditions or with alternative amines or when high stability needed. This pairing is compliant with the China National Standard specifications for fossil power condensate polishing applications, including the China Strong Osmotic Ball Mill test.	SBA	MACRO	0.80	H ⁺
AmberLite™ HPR2800 H		Yes		SAC	MACRO	1.70	OH ⁻
AmberLite™ 600i	Layer Separation	N/A	Inert interface separator compatible with all PWR condensate polishing resin pairs.	Inert	GEL	N/A	N/A

Key: SBA = Strong Base Anion SAC = Strong Acid Cation MB = Mixed Bed

Powering performance worldwide.

With a large global manufacturing footprint, strong R&D expertise and technical support services and systems, we supply high market volumes with high quality. DuPont partners with you, our customer, to understand unmet needs and develop tailored solutions.

TECHNICAL SERVICE, RESEARCH & DEVELOPMENT

Athlone, Ireland
Edina, MN, USA
Greifenberg, Germany
Huzhou, China
Hyderabad, India
Mexico City, Mexico
Midland, MI, USA
Alphaville, Brazil
Shanghai, China
Singapore
Soma, Japan
Tarragona, Spain*
Wilmington, DE, USA
Windsor, Australia

COMMERCIAL OPERATIONS

Bangkok, Thailand
Beijing, China
Budapest, Hungary
Dubai, UAE
Chengdu, China
Delhi, India
Edina, MN, USA
Freienbach, Switzerland
Greifenberg, Germany
Guangzhou, China
HCM City, Vietnam
Hong Kong, China
Jakarta, Indonesia
Johannesburg, South Africa
Kuala Lumpur, Malaysia
Manila, Philippine
Marlborough, MA, USA
Melbourne, Australia

Mexico City, Mexico
Midland, MI, USA
Milan, Italy
Moscow, Russia
Mumbai, India
Nairobi, Kenya
Neu Isenburg, Germany
Newton, MA, USA
Paris, France
São Paulo, Brazil
Seoul, Republic of Korea
Shanghai, China
Singapore
Surubya, Indonesia
Taipei, China Taiwan
Tokyo, Japan
Warsaw, Poland
Wilmington, DE, USA

MANUFACTURING

Athlone, Ireland
Chauny, France
Edina, MN, USA
Fombio, Italy
Greifenberg, Germany
Huzhou, China
Jubail Industry City, KSA
Midland, MI, USA
Qingpu, China
Soma, Japan
Windsor, Australia

* Global Water
Technology Center

Have a question? Contact us at: [dupont.com/water/contact-us](https://www.dupont.com/water/contact-us)



[dupont.com/water](https://www.dupont.com/water)

No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.

© 2021 DuPont. DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, SM or ® are owned by affiliates of DuPont de Nemours, Inc. unless otherwise noted.

Form No. 45-D00957-en CDP, Rev. 3
October 2021