



Product Data Sheet

AmberTec™ UP7530 Chelating Resin

Semiconductor-grade, Uniform Particle Size, Boron-selective Resin

Description

AmberTec™ UP7530 Chelating Resin is a unique ion exchange resin specifically designed using uniform particle size technology to remove boron for the highest-purity water treatment applications, as those typically required in the microelectronics industry.

The presence of boron compounds, even in very small concentration can create issues for ultrapure water (UPW) systems. AmberTec™ UP7530 has high selectivity for boric acid due to its unique active group. The borate ion makes a very stable complex with the active group while other anions do not react, allowing borate to be removed and held very tightly in the presence of other anions.

AmberTec™ UP7530 has extraordinarily low TOC and high resistivity which enable much shorter rinse-down time, which is critical for ultrapure water (UPW) application resulting in both water and time savings. The high boron selectivity combined with uniform particle size brings higher operating exchange capacity than standard boron removal resins. AmberTec™ UP7530 can bring more flexibility to OEMs and end-users on the process design when stringent boron concentration is required.

Applications

- Selective boron removal

Typical Properties

Physical Properties

Copolymer	Styrene-divinylbenzene
Matrix	Macroporous
Type	Chelant
Functional Group	N-methylglucamine
Physical Form	Off-white, opaque, spherical beads

Chemical Properties

Ionic Form as Shipped	Free base (FB)
Total Exchange Capacity	≥ 0.7 eq/L
Water Retention Capacity	51 – 59%

Particle Size[§]

Particle Diameter	490 – 590 µm
Uniformity Coefficient	≤ 1.1
< 300 µm	≤ 1%
> 850 µm	≤ 3%

Ultrapure Water Performance

Resistivity, 24 h	≥ 15 MΩ·cm
ΔTOC, 24 h	≤ 5 ppb

Density

Shipping Weight	660 g/L
-----------------	---------

[§] For additional particle size information, please refer to the [Particle Size Distribution Cross Reference Chart](#) (Form No. 45-D00954-en).

Suggested Operating Conditions


Recommended Operating Temperature 15 – 25°C (59 – 77°F)
 Recommended Service Flowrate 40 – 60 BV*/h

* 1 BV (Bed Volume) = 1 m³ solution per m³ resin or 7.5 gal per ft³ resin

Hydraulic Characteristics

Pressure drop data for AmberTec™ UP7530 Chelating Resin in water as a function of service flowrate is shown in Figure 1. These pressure drop expectations are valid for clean beds which have not been contaminated with suspended solids during the service run; if the bed accumulates solids, the pressure drop will increase.


Figure 1: Pressure Drop
 Temperature = 10 – 60°C (50 – 140°F)



UPW Rinse Properties

AmberTec™ UP Ion Exchange Resins are especially processed and controlled in Quality to ensure the purest treated water quality for semiconductors applications. A typical rinse-down curve for TOC as a function of rinse volume (in bed volumes) based on our quality control procedure for AmberTec™ UP7530 resin is shown in Figure 2.

Figure 2: TOC Rinse-down



Product Stewardship

DuPont has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our product stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our product stewardship program rests with each and every individual involved with DuPont products—from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice

DuPont strongly encourages its customers to review both their manufacturing processes and their applications of DuPont products from the standpoint of human health and environmental quality to ensure that DuPont products are not used in ways for which they are not intended or tested. DuPont personnel are available to answer your questions and to provide reasonable technical support. DuPont product literature, including safety data sheets, should be consulted prior to use of DuPont products. Current safety data sheets are available from DuPont.

Please be aware of the following:

- **WARNING:** Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.

Have a question? Contact us at:

www.dupont.com/water/contact-us

All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.

© 2022 DuPont. DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, SM or ® are owned by affiliates of DuPont de Nemours Inc., unless otherwise noted.

