



FilmTec™ HSRO-4040-FF

Heat Sanitizable Reverse Osmosis Element

Key Features

- Delivers outstanding quality water with the added capability to withstand sanitization with hot water to eliminate the need for chemical sanitizers.
- High active membrane area that allows system design with either lower operating flux or cost savings from fewer membrane elements.
- Full-fit configuration design that minimizes stagnant areas for sanitary designs.
- All components comply with FDA standards.

Key Applications

- Purified water in the pharmaceutical, medical, and biotechnology applications
- Permeate polishing in food and dairy processes.

Typical Properties

FilmTec™ Element	Active Area ft ² (m ²)	Stabilized Permeate Flow Rate gpd (m ³ /d)	Stabilized Salt Rejection %
HSRO-4040-FF	90 (8.4)	2,900 (11)	97

1. Permeate flow and salt rejection based on the following test conditions: 2,000 ppm NaCl, 125 psi (8.6 bar), 77°F (25°C), pH 8, and 15% recovery **before any heat treatment**.
2. Permeate flow for individual elements may vary ±20%.
3. Sales specifications may vary as design revisions take place.



Exemplary Projections

For optimal performance, elements must be pre-conditioned by exposure to hot water prior to initial use. An initial flux loss and rejection increase will occur after pre-conditioning. An exact percentage of these performance change is difficult to predict since it depends on many factors and can differ from system to system. For more information about projected performance and DuPont's recommended protocol for element pre-conditioning refer to [Heat Sanitization](#) (Form No. 45-D01632-en).

FilmTec™	Feed Pressure psi (bar)	Average Flux gfd (lmh)	Calculated Permeate Flow gph (m ³ /h)	Recovery (%)	Feed TDS (NaCl ppm)	Calculated Permeate TDS (ppm)	Calculated Rejection (%)
HSRO-4040-FF	135 (9.3)	15 (26)	1,056 (4)	75	500	11.11	97.8

1. Results are based on WAVE modeling **after heat treatment** of a 2-stages (2:1) system with 6-element pressure vessel, operated at 77°F (25°C), pH 7, feed flow 1,400 gph (5.33 m³/h) and a Flow Factor 0.85
2. WAVE version: contact your DuPont representative for more help with projections.
3. No warranty is provided for the application of this information since use conditions and applicable laws may differ from one location to another and may change with time
4. Piloting will give the best performance approach for any specific application.

Element Dimensions



DuPont supplies two end caps (part number 102109) with each HSRO-4040-FF element. DuPont sells coupler part number 89048 for use in multiple element housings. Each coupler includes two 2-210 EPR O-rings (part number 89255).

FilmTec™ Element HSRO-4040-FF Dimensions – inches (mm)	
A	40.0 (1,016)
B	0.75 OD (19)
C	3.9 (99)

OD - Outer Diameter

1. Refer to [FilmTec™ Design Guidelines for multiple-element systems of midsize elements](#) (Form No. 45-D01588-en).
2. Fits nominal 4 inch I.D. pressure vessels.

Suggested Operating Conditions

Membrane Type	Polyamide Thin-Film Composite
Maximum Operating Temperature ^a	113°F (45°C)
Maximum Sanitization Temperature (@ 25 psig)	185°F (85°C)
Maximum Operating Pressure	600 psig (41 bar)
Maximum Pressure Drop	
Per Element	15 psig (1.0 bar)
Per Vessel (Housing)	60 psig (4.1 bar)
pH Range	
Continuous Operation ^a	2 – 11
Short-Term Cleaning ^b	1 – 12
Maximum Feed Silt Density Index (SDI)	SDI 5
Free Chlorine Tolerance ^c	< 0.1 ppm

General Information

- Keep elements moist at all times after initial wetting.
- For successful operation of Reverse Osmosis (RO) and Nanofiltration (NF) membrane systems, the operation must follow the guidelines provided in the [FilmTec™ Reverse Osmosis / Nanofiltration Elements Operation Excellence and Limiting Conditions Tech Fact](#) (Form No. 45-D04388-en).
- To prevent biological growth during prolonged system shutdowns, it is recommended that membrane elements be immersed in a preservative solution.
- The customer is fully responsible for the effects of incompatible chemicals and lubricants on elements.
- Avoid static permeate-side backpressure at all times.
- Permeate obtained from the first hour of operation should be discarded.
- The use of this product in and of itself does not necessarily guarantee the removal of cysts and pathogens from water. Effective cyst and pathogen reduction is dependent on the complete system design and on the operation and maintenance of the system.
- Avoid any abrupt pressure or cross-flow variations on the spiral elements during start-up, shutdown, cleaning or other sequences to prevent possible membrane damage.
- During start-up, a gradual change from a standstill to operating state is recommended as follows:
 - Feed pressure should be increased gradually over a 30-60 second time frame.
 - Cross-flow velocity at set operating points should be achieved gradually over 15-20 seconds.
- Suitable quality water must be used during all pre-conditioning steps. This water is chlorine-free, non-scaling/fouling water. RO permeate is preferred, but prefiltered municipal water may be used.

Important Information

Please consider good operating practices for the optimal performance of the Reverse Osmosis membrane elements to assure damage free operation:

1. [Loading of Pressure Vessels - Preparation & Element Loading](#) (Form No. 45-D01602-en)
2. System Operation, including plant [Start-Up Sequence](#) (Form No. 45-D01609-en) and [RO & NF Systems Shutdown](#) (Form No. 45-D01613-en)
3. [Handling, Preservation, and Storage](#) (Form No. 45-D03716-en)

Full information of plant design, system operation, and troubleshooting is given in the [FilmTec™ Reverse Osmosis Membranes Technical Manual](#) (Form No. 45-D01504-en).

Regulatory Note

These products are listed to NSF/ANSI 61. For more information visit:

<http://www.nsf.org/Certified/PwsComponents/Listings.asp?Company=0N280&Standard=061>



All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.

Have a question? Contact us at:
www.dupont.com/water/contact-us

© 2023 DuPont. DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, SM or ® are owned by affiliates of DuPont de Nemours Inc., unless otherwise noted.

Form No. 45-D01511-en, Rev. 8
January 2023