

DuPont™ IntegraTec™ XP 51 IG Module

Modules for Open Platform

Key Features

Proven XP™ Hydrophilic PVDF Fiber:

- Superior fouling and chlorine resistance.
- High colloidal particulate, bacteria and virus log removal rate.
- Excellent filtration permeability.
- Easy cleaning and wettability.

Optimized Module Design:

- Open platform design to fit customer built skids.
- Short module design to suit height restricted or containerized installation.
- High operation recovery with high air scouring tolerance.
- Reduced chemical consumption with maintenance cleanings protocol.
- Robust materials for long lifetime.
- Easy installation and low maintenance.

Key Applications

High recovery, height restricted, or containerized filtration in:

- Industrial utility water.
- Industrial wastewater reuse.
- Municipal wastewater filtration.
- RO pretreatment.



Module Specification

General

| | |
|--------------------------------|-----------------------------------|
| Part No / GMID | 12091623 |
| Mode of Filtration | Out-In Pressurized |
| Membrane Type | Hollow fiber |
| Membrane Material | PVDF (Polyvinylidene Fluoride) |
| Membrane Pore Size | 0.03 µm |
| Module Operating Process | Dead-end |
| Other Wetted Module Components | Polyurethane, uPVC, EPDM, and ABS |

Dimensions


| | | |
|-------------------------------|-------------------|---------------------|
| Active Membrane Area | 51 m ² | 549 ft ² |
| Module Length Overall (L) | 1,863 ± 3 mm | 73.3 ± 0.1 inch |
| Module Length (L1) | 1,500 ± 1.5 mm | 59.1 ± 0.1 inch |
| Module Length (L2) | 1,633 ± 3.0 mm | 64.3 ± 0.1 inch |
| Module Length (L3) | 1,823 ± 3.0 mm | 71.8 ± 0.1 inch |
| Module Diameter (D) | 225 mm | 8.9 inch |
| Module Width (W1) | 180 mm | 7.1 inch |
| Module Width (W2) | 342 mm | 13.5 inch |
| Feed / Filtrate port DN50 (F) | 51 mm | 2 inch |

Weight and Volume

| | | |
|--|-------|----------|
| Shipping Weight | 60 kg | 132 lbs. |
| Weight Empty | 48 kg | 106 lbs. |
| Weight Filled | 83 kg | 183 lbs. |
| Hold-Up Volume Feed (Clean-In-Place = CIP) | 30 L | 7.9 gal |
| Hold-Up Volume Membrane Structure (CIP) | 9 L | 2.4 gal |
| Hold-Up Volume Filtrate (CIP) | 8 L | 2.1 gal |

Suggested Operating Conditions

| General | Details | |
|--|--------------------------------|----------------|
| Operating Temperature Range | 1 - 40 °C | 34 - 104 °F |
| Operating pH | 2 - 11 | |
| Cleaning pH | 2 - 12 | |
| Typical Filtration Trans-Membrane Pressure (TMP) | 0.4 - 1.5 bar | 5.8 - 21.8 psi |
| Typical Backwash TMP | 0.6 - 2.0 bar | 8.7 - 29.0 psi |
| Backwash Type | Air scour with liquid backwash | |
| Backwash Flux | 100 L/(m ² h) | 58.8 gfd |
| Backwash Flow | 5.1 m ³ /h | 22.4 gpm |
| Operating Limits (Maximum) | | |
| Rate of Pressure Change | 0.5 bar/sec | 7.3 psi/sec |
| Inlet Pressure | 6.25 bar (at 20 °C) | 90.7 psi |
| Filtration TMP | 2.1 bar | 30.5 psi |
| Backwash TMP | 2.5 bar | 36 psi |
| Filtration Flux | 110 L/(m ² h) | 64.5 gfd |
| Filtration Flow | 5.6 m ³ /h | 24.8 gpm |
| Backwash Flux | 120 L/(m ² h) | 70.6 gfd |
| Particle Size | 300 µm | |
| Exposure NaOCl | ≤ 1,500,000 ppm x h | |
| Recommended max. instantaneous exposure NaOCl | 2,000 ppm | |



General Information

- Avoid any abrupt pressure variations during start-up, operation, shutdown, cleaning or other sequences to prevent possible membrane damage. The maximum pressure change allowable is (0.5 bar/s).
- For assembly please refer to the latest version of the [DuPont™ IntegraTec™ Open Platforms PVDF-UF Modules Assembly Manual](#) (Form No.45-D02507-en).
- If operating limits and guidelines given in this document are not strictly followed, any warranty will be null and void.
- To control biological growth during extended system shutdowns, it is recommended that storage solution be introduced into the membrane modules.

Regulatory Note

- Certified drinking water modules require specific conditioning procedures prior to producing potable water. For operating parameters, please refer to the [DuPont™ IntegraTec™ Process and Design Manual](#) (Form No. 45-D00874-en).
- Drinking water modules may be subjected to additional regulatory restrictions in some countries. Please check local regulatory guidelines and application status before use.
- Flushing needs to be done according to the [DuPont™ IntegraTec™ Open Platforms PVDF-UF Modules Assembly Manual](#) (Form No. 45-D02507-en).



Have a question? Contact us at:
[dupont.com/water/contact-us](https://www.dupont.com/water/contact-us)

All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DUPONT ASSUMES NO OBLIGATION OR LIABILITY FOR THE INFORMATION IN THIS DOCUMENT. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.

DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, SM or ® are owned by affiliates of DuPont de Nemours, Inc. unless otherwise noted. © 2026 DuPont. All rights reserved

Form No. 45-D03865-en, Rev. 9
 January 2026