



IC105S option CS

DuPont™ Tyvek® IsoClean®

DuPont™ Tyvek® IsoClean® Coverall. Serged Seams. Attached Elastic Hood. Set Sleeve Design. Elastic Wrists and Ankles. Attached Thumb Loops. Zipper Closure. Attached Boots with PVC Soles. Semi-auto locking slider zipper pull. White.

[Certificates of Sterility Available Here](#)

Name	Description
Full Part Number	IC105SWHxx0025yy (xx=size)
Fabric/Materials	Tyvek® IsoClean®
Design	Coverall with Attached Hood and Attached Boots,Hooded Coverall
Seam	Serged
Color	White
Quantity/Box	25 per case
Sizes	MD, LG, XL, 2X, 3X
Option Codes	CS

FEATURES & PRODUCT DETAILS

Tyvek® IsoClean® delivers an ideal balance of protection, durability and comfort. Made using a patented flash spinning process, Tyvek® provides an inherent barrier to particles, microorganisms and non-hazardous light liquid splash.


- Clean-processed garments offer lowest level of particle shedding within DuPont product portfolio
- Serged seams have multiple interlocking threads that are sewn around the raw edges of garment material to create a strong, stress-resistant seam.
- Coverall has elastic openings for tighter fit at wrist and ankle.
- Attached hood with elastic around face opening.
- Attached thumb loops to minimize bunching of sleeves.
- Front zipper closure for easy donning and doffing.
- Attached boots with PVC soles that provide enhanced skid-resistance and durability.
- Full traceability on all sterilized apparel with [Certificates of Sterility Available Here](#).
- Zipper features a semi-automatic locking slider allowing the puller to stay down and in a locked position

AVAILABLE OPTIONS

Option Code	Description	Sizes	Part Number
CS	Clean-Processed & Sterile	MD,LG,XL,2X,3X,4X,5X	IC105SWH5X0025CS

SPECIFICATIONS

- The garment shall be constructed of DuPont™ Tyvek® 400-- a patented flash-spun polyethylene fabric.
- The garment shall be white in color.
- The garment shall be a hooded coverall design.
- The garment shall have serged seams.
- The garment shall have set sleeves.
- The garment shall have a front zipper closure.
- The garment shall have attached thumb loops.
- The garment shall be clean-processed and sterile.
- The garment shall have soles made of PVC.



FINISHED DIMENSIONS

Size	Sleeve Length	Chest Width	Inseam	Fits Chest	Fits Height	Boot Length	Mens Shoe	Womens Shoe
MD	33 1/4	24 1/4	28	35 1/4 - 38 3/4	5'3" - 5'7"	11 3/4	7	9
LG	35	25 3/4	29	38 1/4 - 41 3/4	5'5" - 5'9"	13 1/4	11	13
XL	36 1/2	27 1/4	29 1/2	41 1/4 - 44 3/4	5'8" - 6'2"	14 3/4	15	17
2X	38 1/4	28 3/4	30 1/2	44 1/4 - 47 3/4	6'0" - 6'4"	14 3/4	15	17
3X	38 1/2	30 1/4	31 1/2	47 1/4 - 50 3/4	6'2" - 6'4"	14 3/4	15	17
4X	39	31 3/4	32 1/2	50 1/4 - 53 3/4	6'4" - 6'7"	14 3/4		
5X	40 1/4	33 3/4	33 1/2	54 1/4 - 57 3/4	6'7" - 6'10"	14 3/4		

ADDITIONAL EQUIPMENT NEEDED

- Wear other appropriate PPE such as, but not limited to, respiratory, eye, head, hand, and foot protection based on the hazard assessment.

Physical Properties



Data relating to mechanical performance of the fabrics used in DuPont chemical protective clothing, listed for the selected garment according to the test methods and relevant European standard, if applicable. Such properties, including abrasion and flex-cracking resistance, tensile strength and puncture resistance can help in the assessment of protective performance.

Property	Test Method	Typical Result	stdDev
Basis Weight	ASTM D3776	1.33 oz/yd ²	0.06 oz/yd ²
Burst Strength - Mullen.	ASTM D774	44 psi	7 psi
Breaking Strength - Grab (MD).	ASTM D5034	14 lb _f	2 lb _f
Breaking Strength - Grab (CD)	ASTM D5034	20 lb _f	3 lb _f
Particle Shedding (Helmke Drum)	IEST-RP-CC003.3	Category I	
Bacterial Filtration Efficiency (3.0 micron)	ASTM F2101	98.4 %	0.9 %
Hydrostatic Head	AATCC 127	74 cm H ₂ O	10 cm H ₂ O
Wearing Apparel Flammability	16 CFR 1610	Class 1	

CLEANROOM WARNINGS

- Anyone who begins to exhibit allergic response during the use of DuPont products should immediately cease using these products. The incident should also be reported to DuPont at 1.800.441.3637.
- Latex Statement: As of January 1, 2006, DuPont production specifications exclude use of components containing natural rubber latex in the manufacture of Dupont™ Tyvek® IsoClean®, Tyvek™ Micro-Clean® 2-1-2 and ProClean® garments, and DuPont™ ProShield® 10 and DuraTrac™ shoe covers. Notwithstanding, DuPont™ Tyvek® Micro-Clean® 2-1-2 and Duratrac™ shoe covers produced by Cardinal Health prior to May 2008 may contain dry crumb natural rubber latex.
- Silicone Statement: In the past, DuPont has found that threads and zippers can be the most significant source of silicone oil contamination in garments. DuPont specifies that thread and zippers used in Dupont™ Tyvek® IsoClean® and ProClean® garments be manufactured without the use of silicone oils. Notwithstanding, DuPont cannot guarantee the absence of silicone oils on these garments, nor can DuPont confirm silicone oil prohibition in DuPont™ Tyvek® Micro-Clean® 2-1-2 produced by Cardinal Health prior to May 2008. For end uses with concerns about contamination with silicone oils or any other contaminants, the best practice is to audit inbound materials, including garments, for those contaminants.
- Warning: Cleanroom apparel should not be used around heat, flames, sparks or in potentially flammable or explosive environments. Cleanroom fabrics should have slip-resistant materials on the outer sole of boots, shoe covers, or other garment surfaces in conditions where slipping could occur.

SPECIAL WARNINGS

- Seams and closures have less barrier than fabric.
- Note: for protection from hazardous or infectious liquids, additional barrier tests are required to establish suitability for use.
- *CAUTION: This information is based upon technical data that DuPont believes to be reliable. It is subject to revision as additional knowledge and experience are gained. DuPont makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics, not complete garments, under controlled conditions. It is intended for informational use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact DuPont for specific data. If fabric becomes torn, abraded or punctured, or if seams or closures fail, or if attached gloves, visors, etc. are damaged, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including, without limitation, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of DuPont or others covering any material or its use.

Cellosolve® and Selexol™ are registered trademarks of Dow Chemicals Company. Skydrol® is a registered trademark of Solutia.

- Data presented does not comprise a product specification.